



PATRIOT® 15-Ton Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT46LW18V](#)



PATRIOT® 15-Ton Covered C-Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	2.6Ah 18V NiMH
Catalog Number	PAT46LW18V
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810654613
UPC 12 Digit	7818106546133

Dimensions

Dimensions	18.65 in x 3.70 in x 13.75 in
Height	13.75 in
Jaw Width	2.00 in
Length	18.65 in
Weight	17.5 lb
Width	3.7 in

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance UI Status

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_PAT46LW_LineArt](#)
[Sales Drawings - 50024452](#)
[SDS - NI-MH 18V and 14V MAKITA BATTERY SDS \(2014-12\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-PAT46LW18V-SPEC-EN | REV 6/2024