



PATRIOT® T3 Technology 15-Ton Battery Crimper, Latch Head, Uncovered, two 3.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Nylon Pro Bag

By Burndy
Catalog # [PAT46T3LU03D3](#)



PAT46T3 Tech 15T Battery Crimper, Latch Head, Uncovered, 3Ah Li-Ion, DC, Nylon Pro Bag.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46T3LU03D3
Container Type	Nylon Pro Bag
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Power Source	12V-DC Charger
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper, T3 Technology
Type	Crimper
UPC	621945625433

Dimensions

Dimensions	18.59 in x 3.26 in x 15.18 in
Height	15.18 in
Length	18.59 in
Weight	16 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

Logistics

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50110717](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-PAT46T3LU03D3-SPEC-EN | REV 6/2024