



**PATRIOT® T3 Technology 15-Ton
Battery Crimper, C-Head, Rubber
Covered, two 3.0Ah 18V Li-Ion
Batteries, 120V-AC Charger, Hard
Case**

By Burndy
Catalog # [PAT46T3SC03A2](#)



PAT46T3 Tech 15T Battery Crimper, C-Head, Rubber Covered,
3Ah Li-Ion, AC, Hard Case.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46T3SC03A2
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADPI Adapter
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper, T3 Technology
Type	Crimper
UPC	621945625594

Dimensions

Dimensions	18.44 in x 3.26 in x 14.13 in
Height	14.13 in
Length	18.44 in
Weight	19.45 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	---

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	--

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50110709](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.