



**PATRIOT® T3 Technology 15-Ton  
Battery Crimper, C-Head, Rubber  
Covered, two 3.0Ah 18V Li-Ion  
Batteries, 120V-AC Charger, Nylon  
Pro Bag**

By Burndy  
Catalog # [PAT46T3SC03A3](#)



PAT46T3 Tech 15T Battery Crimper, C-Head, Rubber Covered,  
3Ah Li-Ion, AC, Nylon Pro Bag.

**Application**

Crimping

**General**

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46T3SC03A3
Container Type	Nylon Pro Bag
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper, T3 Technology
Type	Crimper
UPC	621945625655

**Dimensions**

Dimensions	18.44 in x 3.26 in x 14.13 in
Height	14.13 in
Length	18.44 in
Weight	19.45 lb
Width	3.26 in

**Electrical Ratings**

Operating Voltage	18 VDC
-------------------	--------

**Conductor Related**

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	---

**Logistics**

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50110709](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.