



# PATRIOT® T3 Technology 15-Ton Battery Crimper, C-Head, Uncovered, two 3.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog Number [PAT46T3SU03A2](#)



PAT46T3 Tech 15T Battery Crimper, C-Head, Uncovered, 3Ah Li-Ion, AC, Hard Case.

## Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 2" jaw opening with 355° head rotation
- Uses P Dies and U Dies with PUADP1 Adapter
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper, T3 Technology
Type	Crimper
UPC	621945625488

## Dimensions

Dimensions	18.44 in x 3.26 in x 14.13 in
Height	14.13 in
Length	18.44 in
Weight	18.15 lb
Width	3.26 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

## Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50110709](#)  
[SDS - Burndy BAT18VLI SDS Sheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-PAT46T3SU03A2-SPEC-EN | REV 5/2023

