



# PATRIOT® 6-Ton Scissor Action, D3 Crimp Jaw, No Batteries, No Charger, Hard Case

By Burndy  
Catalog # PAT500SJ66LILCB

PATRIOT® 6-Ton Scissor Action, D3 Crimp Jaw, No Batteries, No Charger, Hard Case.



## Application

Crimping and Cutting

## General

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	No Charger
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	781810673799
UPC 12 Digit	7818106737999

## Dimensions

Dimensions	16.80 in x 2.90 in x 13.40 in
Height	13.4 in
Length	16.8 in
Weight	10.1 lb
Width	2.9 in

## Conductor Related

Crimping Ranges	Copper: #10 sol. - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #14 sol. - 350 kcmil; ACSR: #14 sol. - 4/0 AWG
-----------------	---

## Certifications And Compliance

Standards - RoHS Compliance UI Status

## Logistics

Package Contents	Tool, D3 Crimp Jaw, Lanyard, Hard Case
------------------	--

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50024949](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-PAT500SJ66LILCB-SPEC-EN | REV 6/2024