



# PATRIOT® 11-Ton Dieless Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog # PAT644XT18V



PATRIOT® 11-Ton Dieless Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case.

## Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	2.6Ah 18V NiMH
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810450697
UPC 12 Digit	7818104506977

## Dimensions

Dimensions	15.65 in x 3.5 in x 13.9 in
Height	13.9 in
Length	15.65 in
Weight	16.5 lb
Width	3.5 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Copper Flex: #2 AWG - 777 kcmil; Aluminum: #6 AWG - 900 kcmil; ACSR #4 AWG - 556.5 kcmil
-----------------	---

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
Standards - RoHS Compliant	Yes

## Product Assets

[3D Models - PAT644XT18V\\_MODEL-IGES](#)  
[3D Models - PAT644XT18V\\_MODEL-PDF](#)  
[3D Models - PAT644XT18V\\_MODEL-STEP](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_PAT644XT18V\\_LineArt](#)  
[Sales Drawings - 10062240](#)  
[SDS - NI-MH 18V and 14V MAKITA BATTERY SDS \(2014-12\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-PAT644XT18V-SPEC-EN | REV 5/2024