



PAT750XT18V

By Burndy
Catalog # [PAT750XT18V](#)

PATRIOT® 12-Ton C-Head Battery Crimper, Hydraulic Self-Contained, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case.



Application

Crimping

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	2.6Ah 18V NiMH
Catalog Number	PAT750XT18V
Container Type	Hard Case
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810438701
UPC 12 Digit	7818104387011

Dimensions

Dimensions	15.75 in x 3.50 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	16.5 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_082_OYPF_PAT50XT18V_lineart](#)
[Sales Drawings - 10046982](#)
[SDS - NI-MH 18V and 14V MAKITA BATTERY SDS \(2014-12\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-PAT750XT18V-SPEC-EN | REV 6/2024