



# PATRIOT® 129 Series Latch Head Battery Cutter, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog Number [PATCUT129ACSR18V](#)



PATRIOT® 7-Ton Latch Head, Battery Actuated Cutter, up to 1113 kcmil ACSR & 1.29" CU/AL, (2) 2.6Ah NiMH Batteries, 120V-AC Charger, Hard Case.

## Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

## Application

Cutting

## General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	2.6Ah 18V NiMH
Container Type	Hard Case
Crimp Force Capacity	7 ton
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	781810370803
UPC 12 Digit	7818103708033

## Dimensions

Dimensions	14.50 in x 3.70 in x 12.80 in
Height	12.80 in
Length	14.50 in
Weight	12.0 lb
Width	3.70 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum up to 1.29"; ACSR up to 1113 kcmil; Ground Rod up to 5/8"; Rebar up to 1/2"; Soft Steel Bolts up to 5/8"; Standard Guy up to 1/2"; EHS Guy Strand up to 3/8"
-----------------	--

## Certifications and Compliance

Standards - RoHS Compliance EX Status

## Product Assets

- [3D Models - PATCUT129ACSR18V\\_MODEL-STEP](#)
- [3D Models - PATCUT129ACSR18V\\_MODEL-PDF](#)
- [3D Models - PATCUT129ACSR18V\\_MODEL-IGES](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 10046860](#)
- [SDS - NI-MH18Vand14VMAKITABATTERYMSDS](#)



A proud member of the Hubbell Family.