



PATRIOT® 2156 Series Latch Head Battery Cutter, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PATCUT215618V](#)

PATRIOT® 10-Ton Latch Head, Battery Actuated Cutter, up to 2156 kcmil ACSR, (2) 2.6Ah NiMH Batteries, 120V-AC Charger, Hard Case.



Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	2.6Ah 18V NiMH
Catalog Number	PATCUT215618V
Container Type	Hard Case
Crimp Force Capacity	10 ton
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	781810649541
UPC 12 Digit	7818106495411

Dimensions

Dimensions	16.52 in x 3.27 in x 13.29 in
Height	13.29 in
Length	16.52 in
Weight	16.3 lb
Width	3.27 in

Electrical Ratings

Operating Voltage 18 VDC

Conductor Related

Crimping Ranges Cutting Capacity:
Copper/Aluminum up to 2.0";
ACSR up to 2156 kcmil;
Ground Rod up to 3/4"; Rebar
up to 5/8"; Soft Steel Bolts up
to 3/4"; Standard Guy up to
9/16"; EHS Guy Strand up to
9/16"

Certifications And Compliance

Standards - RoHS Compliance UI
Status

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_PATCUT2156-18V_LineArt](#)
[Sales Drawings - 50024459](#)
[SDS - LITHIUM-ION BATTERY SDS \(2015-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-PATCUT215618V-SPEC-EN | REV 6/2024