



# PATRIOT® 2156 Series Latch Head Battery Cutter, No Batteries, No Charger, Hard Case

By Burndy  
Catalog # [PATCUT2156LILCB](#)



PATRIOT® 10-Ton Latch Head, Battery Actuated Cutter, up to 2156 kcmil ACSR, No Batteries, No Charger, Hard Case.

## Application

Cutting

## General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT2156LILCB
Container Type	Hard Case
Crimp Force Capacity	10 ton
Power Source	No Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	781810648872
UPC 12 Digit	7818106488722

## Dimensions

Dimensions	16.46 in x 3.27 in x 13.66 in
Height	13.66 in
Length	16.46 in
Weight	14.1 lb
Width	3.27 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges Cutting Capacity:  
Copper/Aluminum up to 2.0";  
ACSR up to 2156 kcmil;  
Ground Rod up to 3/4"; Rebar  
up to 5/8"; Soft Steel Bolts up  
to 3/4"; Standard Guy up to  
9/16"; EHS Guy Strand up to  
9/16"

## Certifications And Compliance

Standards - RoHS Compliance UI  
Status

## Logistics

Package Contents Cutter, Lanyard, Hard Case

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50002799](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.