



PATRIOT® IN-LINE® 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag

By Burndy
Catalog Number [PATMD6LW](#)

PATMD-LW IN-LINE® 6T Scissor Action, BG/D3 Crimp Jaw, 3Ah Li-ion, AC, Utility Bag.



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

General

Application - For Use On	Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Vinyl Utility Bag
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945467323
UPC 12 Digit	621945467323

Dimensions

Dimensions	18.73 in x 4.375 in x 2.75 in
Height	2.75 in
Length	18.73 in
Weight	5.55 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	With Appropriate Jaw: Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"
-----------------	---

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Tool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Utility Bag

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PATMD-LW](#)
- [Sales Drawings - 50054521](#)
- [SDS - Burndy BAT18VLI SDS Sheet](#)



A proud member of the Hubbell Family.

