



PATRIOT® IN-LINE® 6-Ton Scissor Action, Cutter Jaw CU/AL Replacement Blade Set

By Burndy
Catalog # [PATMDCUTCUALKIT](#)



PATRIOT® IN-LINE® 6-Ton Scissor Action Cutter Jaw CU/AL Replacement Blade Set (Contains 2 Blades Only).

Application

Crimping and Cutting

General

Application - For Use On	Cutting Aluminum and Copper Cable
Catalog Number	PATMDCUTCUALKIT
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	120V-AC Charger
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945491663
UPC 12 Digit	621945491663

Dimensions

Weight	0.45 lb
--------	---------

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter Jaw CU/AL Replacement Blade Set (Contains 2 Blades only) for PATMD-LW Cutter Jaw

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-PATMDCUTCUALKIT-SPEC-EN | REV 6/2024