

PATMDCUTCUALKIT

Par Burndy

No de catalogue [PATMDCUTCUALKIT](#)

PATRIOT® IN-LINE® 6 tonnes mâchoire de coupe à action de ciseaux CU/AL jeu de lames de rechange (contient 2 lames seulement).



Caractéristiques

- Lames uniques CU/AL pour PATMDCUTCLWJAW

Général

Application - pour utilisation sur	Cutting Aluminum and Copper Cable
Capacité de force de sertissage	6 ton
Catalog Number	PATMDCUTCUALKIT
Nom de commerce	PATRIOT® IN-LINE®
Source d'alimentation	120V-AC Charger
Type	Crimper and Cutter
Type d'outil	Battery Actuated Scissor Action
Type de matrice	W Die and X Die
UPC	621945491663
UPC 12 Digit	621945491663

Dimensions

Poids	0.45 lb
-------	---------

Caractéristiques électriques

Tension de fonctionnement	18 VDC
---------------------------	--------

Lié au conducteur

Plages de sertissage	Cutting Capacity: Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil
----------------------	---

Logistique

Contenu de l'emballage	Cutter Jaw CU/AL Replacement Blade Set (Contains 2 Blades only) for PATMD-LW Cutter Jaw
Nombre de paquets minimum	1

Documentation

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)