



## PENA5GAL, Oxide Inhibitor, 5 Gallon Container

By Burndy  
Catalog # [PENA5GAL](#)

Electrical Joint Compound, 5 Gallon Steel Pail, 28/26 Gauge-Black, For Al-Al and Al-Cu Connectors ,Grounding, Cu Conduit Threads.



### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA5GAL
Container Type	Pail
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810592830
UPC 12 Digit	7818105928300
Viscosity at 100 Fahrenheit	305 °F

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Container Size	5 Gallon
----------------	----------

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENAGAL\\_LineArt](#)
- [Sales Drawings - 50016091](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)



A Hubbell brand