



PENEGAL, Oxide Inhibitor, Gallon Container

By Burndy
Catalog # [PENEGAL](#)

Electrical sealing compound, For Use On-Application: Copper to Copper.



General

Application - For Use On	Copper to Copper
Catalog Number	PENEGAL
Container Type	Can
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810593509
UPC 12 Digit	7818105935099
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 Gallon
----------------	----------

Product Assets

- [3D Models - PENEGAL_MODEL-STEP](#)
- [3D Models - PENEGAL_MODEL-PDF](#)
- [3D Models - PENEGAL_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENEQT_LineArt](#)
- [SDS - PENETROX E PORTUGUESE SDS](#)
- [SDS - PENETROX E ESPANOL SDS](#)
- [SDS - PENETROX E FRENCH SDS](#)
- [SDS - PENETROX E RUSSIAN SDS](#)
- [SDS - PENETROX E SDS](#)
- [SDS - PENETROX E GERMAN SDS](#)
- [SDS - PENETROX E Polish SDS](#)



A Hubbell brand