



PGN1025X03D, Nylon Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [PGN1025X03D](#)



Nylon Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03).

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

General

Catalog Number	PGN1025X03D
Connector Type	Male/Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293119
UPC 14 Digit GTIN	00781810293119

Dimensions

Dimension - B Length fraction	0.27
Dimension - B Length inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

- [3D Models - PGN1025X03D_MODEL-STEP](#)
- [3D Models - PGN1025X03D_MODEL-IGES](#)
- [3D Models - PGN1025X03D_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094219](#)
- [Specifications - PGN1025X03D Specification Sheet French](#)
- [Specifications - PGN1025X03D Specification Sheet English](#)