



## Hydraulic Hose, 15', 3/16" dia non-cond, Stackable couplers (male/female), Orange, 10,000 psi

By Burndy  
Catalog # [PT2990015](#)

Hydraulic hose, 15', 3/16" dia non-cond, Stackable couplers (male/female), Orange, Min burst pressure 40,000 psi, Nom working pressure 10,000 psi.



### Application

Accessory

### General

Catalog Number	PT2990015
EU RoHS Indicator	Yes
Type	Hydraulic Hose
UPC	781810008461

### Certifications And Compliance

Standards - RoHS Compliance EX  
Status

### Logistics

Package Contents Hose, Couplers

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE088658-01\\_A](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-PT2990015-SPEC-EN | REV 6/2024