



Vinyl Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [QP10F250D](#)



MATERIAL: TIN-PLATED BRASS. 600 VOLTS MAX. 105 C MAX.

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

General

Catalog Number	QP10F250D
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810020623
UPC 12 Digit	7818100206233

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - F Width Center to Center inch	0.11 in
Dimension - Length Overall inch	1.00 in
Dimension - Thread Size	-
Dimension - Width inch	0.29 in
Dimension - Width mm	7 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry	UL467
Standards Met	
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

[3D Models - QP10F250D_MODEL-IGES](#)
[3D Models - QP10F250D_MODEL-STEP](#)
[3D Models - QP10F250D_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD214284-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-QP10F250D-SPEC-EN | REV 6/2024

