



QPX4434, Heavy Duty Copper Tapping Connector, Run: 500-1000 kcmil, Tap: 250-500 kcmil

By Burndy
Catalog # [QPX4434](#)

VERSITAP™ Mechanical Parallel Clamp for Copper;
Accommodates: Run: 500 - 1000 kcmil; Tap: 250 - 500 kcmil.



Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections

General

Catalog Number	QPX4434
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810345504
UPC 12 Digit	7818103455044

Dimensions

Dimension - Height fraction	3-1/16
Dimension - Height inch	3.06
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - Width fraction	2-7/16 in
Dimension - Width inch	2.44
Dimension - Width mm	62 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor - Nominal Diameter	0.114, 0.128, 0.144, 0.162, 0.600, 0.630, 0.681, 0.728, 0.772, 0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor Type	• CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[3D Models - QPX4434_MODEL-PDF](#)
[3D Models - QPX4434_MODEL-IGES](#)
[3D Models - QPX4434_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_QPX_PARA_CLAMP_LineArt](#)
[Sales Drawings - sa007887-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-QPX4434-SPEC-EN | REV 6/2024