



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP486A8](#)



Two Conductor 8 IN Spacer, 2167(72/7) kcmil-2156(84/19) kcmil ACSR, 2300 kcmil-2500 kcmil AAC, 550kV.

Application

Substation

General

| | |
|---------------------------------------|----------------------|
| Connector Type | Spacer |
| Installation Torque Recommended in-lb | 480 lbs-in |
| Material | Aluminum Alloy, Cast |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810279472 |
| UPC 12 Digit | 7818102794722 |

Dimensions

| | |
|------------------------------------|----------|
| Dimension - B Length inch | 3.00 in |
| Dimension - Diameter Max Size inch | 1.824 in |
| Dimension - Diameter Min Size inch | 1.737 in |
| Dimension - Width inch | 3.00 in |
| Dimension - Width mm | 76 mm |

Conductor Related

| | |
|---------------------------------|--|
| Conductor - ACSR Str Size | 2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil |
| Conductor - ACSR Str Size Range | 2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil |
| Conductor - AL Str Size | 2300 kcmil;2500 kcmil |
| Conductor - AL Str Size Range | 2300 kcmil-2500 kcmil |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_S2GBPA_BUNDLED_SPACER_LineArt](#)
[Sales Drawings - 10038254](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-S2GBP486A8-SPEC-EN | REV 6/2024