

# Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # [S2GBP48A](#)



Two Conductor 18 IN Spacer, 1590(45/7) kcmil-1750(84/19) kcmil ACSR, 1750 kcmil-2000 kcmil AAC, 550kV.

## Application

Substation

## General

Catalog Number	S2GBP48A
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lbs-in
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810273418
UPC 12 Digit	7818102734188

## Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.632 in
Dimension - Diameter Min Size inch	1.504 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

## Conductor Related

Conductor - ACSR Str Size	1590 (45/7) kcmil;1590 (54/19) kcmil;1750 (54/19) kcmil;1750 (84/19) kcmil
Conductor - ACSR Str Size Range	1590 (45/7) kcmil-1750 (84/19) kcmil
Conductor - AL Str Size	1750 kcmil;1800 kcmil;1900 kcmil;2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section I - Transmission](#)  
[Product Cross Section Image\(s\) - BUR\\_S2GBPA\\_BUNDLED\\_SPACER\\_LineArt](#)  
[Sales Drawings - SD057446-01](#)