

# Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # [S2R496ACG1](#)



Rigid 6 IN Spacer, 3640 kcmil AL Cable, 138kV.

## Application

Substation

## General

Connector Type	Spacer
Installation Torque Recommended in-lb	660 in-lb
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810466834
UPC 12 Digit	7818104668344

## Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.62 in
Dimension - L Length Overall mm	238 mm
Dimension - Length Overall inch	9.38 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

## Conductor Related

Conductor - AL Str Size Range	3640 kcmil
Conductor - Connection Combination	Cable Spacer

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Product Assets

[3D Models - S2R496ACG1\\_MODEL-IGES](#)  
[3D Models - S2R496ACG1\\_MODEL-STEP](#)  
[3D Models - S2R496ACG1\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50066754](#)