



Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN1010BF](#)



Block Fork (Brazed Seam), 12 AWG - 10 AWG, 8-10, 1.02 in L.

Features

- Permits rapid and easy installation of the terminal under the screw head without complete removal of the screw

Application

Power Connector

General

Catalog Number	TN1010BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524091
UPC 12 Digit	7818105240911

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.29 in

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_TN1010BF_LineArt](#)
[Sales Drawings - 50094182](#)



A proud member of the Hubbell Family.