



# Nylon Block Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # [TN1810BF](#)

Block Fork (Braided Seam), 22 AWG - 18 AWG, 8-10, .95 in L, Wire strip length: 3/16".



## Application

Power Connector

## General

Catalog Number	TN1810BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524220

## Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z (inch)	0.32 in

## Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Product Cross Section Image\(s\) - BUR\\_TN1010BF\\_LineArt](#)  
[Sales Drawings - 50094182](#)



A proud member of the Hubbell Family.