



# UC3040, Copper Parallel Groove Clamp, 300-800 kcmil - Either Groove

By Burndy  
Catalog # UC3040



CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 300 - 800 (Either Groove).

## General

Catalog Number	UC3040
Installation Torque Recommended in-lb	480 LBS/in
Plated	N
Plating Type	Unplated
UPC	781810012918

## Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - Height fraction	3-5/16 in
Dimension - Height inch	3.31 in
Dimension - Width fraction	3-1/16 in
Dimension - Width inch	3.06 in

## Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	300 kcmil-800 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_UC\\_PARA\\_CLAMP\\_LineArt](#)  
[Sales Drawings - SA..038990-01](#)



A proud member of the Hubbell Family.