



UC33RS, Cast Aluminum Clamp, Groove A: AL/CU 4/0 Str-400 kcmil ACSR; 3/0-336.4; Groove B: Al/Cu 6 Sol-2/0 Str, ACSR: 6-2/0 with inhibitor

By Burndy
Catalog # [UC33RS](#)



Cast Aluminum Alloy TAPIT™, GROOVE A, AL/CU: 4/0 STR - 400 kcmil ACSR : 3/0 - 336.4 GROOVE B, AL/CU: 6 SOL - 2/0 STR ACSR : 6 - 2/0 W/INHIBITOR.

General

Catalog Number	UC33RS
Installation Torque Recommended in-lb	480 in-lb
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810122556
UPC 12 Digit	7818101225566

Dimensions

Dimension - Height inch	2.77 in
Dimension - Width inch	2.21 in
Dimension - Width mm	56 mm

Conductor Related

Conductor - AL Str Size A Range	4/0 AWG-400 kcmil
Conductor - AL Str Size B	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size B Range	6 AWG-2/0 AWG
Conductor - Copper Str Size A	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Size A Range	4/0 AWG-400 kcmil
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	6 AWG-2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..057342-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-UC33RS-SPEC-EN | REV 6/2024