



Stainless Steel U-Die Kit for Copper Connectors #6 AWG-750 kcmil (15 Sets). Color coded for crimping YA and YS types of connectors

By Burndy
Catalog # [UDIEKITCU](#)



U-Die Kit for Copper, #6 AWG-750 kcmil (15 Sets), for crimping YA and YS.

Application

Crimping

General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Construction Material - Main	Stainless Steel
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Die Kit, Copper
Type	Die
UPC	781810478455
UPC 12 Digit	7818104784555

Dimensions

Dimensions	11.25 in x 7.50 in x 3.00 in
Height	3 in
Length	11.25 in
Width	7.5 in

Conductor Related

Crimping Ranges Copper: #6 AWG - 750 Kcmil

Certifications And Compliance

Standards - RoHS Compliance Status EX

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	(1 each) CASEUDIES15, U5CRT, U4CRT, U2CRT, U1CRT1, U25RT, U26RT, U27RT, U28RT, U29RT, U30RT, U31RT, U32RT, U34RT, U36RT, U39RT
Pallet Quantity	225

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50015897](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-UDIEKITCU-SPEC-EN | REV 6/2024