




VG5, Copper Alloy Vise Connector, 2/0 Str-#3 Sol

By Burndy
Catalog # [VG5](#)

Cu Alloy Vise Connectors, 2/0 Str - #3 Sol.



General

Catalog Number	VG5
Connector Type	Stud Connector
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	WISEIT™
UPC	781810475157

Dimensions

Bolt Size	9/16 in
Dimension - B Length fraction	49/50 in
Dimension - B Length inch	0.94 in
Dimension - Pad Width inch	1.28 in
Dimension - Pin Diameter inch	1.80 in

Conductor Related

Conductor - Copper Solid Run	3 - 2/0
Conductor - Copper Solid Run Range	3 - 2/0
Conductor - Copper Solid Size	3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	3 AWG-2/0 AWG
Conductor - Copper Solid Tap	3 - 2/0
Conductor - Copper Solid Tap Range	3 - 2/0
Conductor - Copper Str Run	3 - 2/0
Conductor - Copper Str Run Range	3 - 2/0
Conductor - Copper Str Tap	3 - 2/0
Conductor - Copper Str Tap Range	3 - 2/0

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	125
-----------------	-----

Product Assets

- [3D Models - VG5_MODEL-STEP](#)
- [3D Models - VG5_MODEL-PDF](#)
- [3D Models - VG5_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_VG_LineArt](#)
- [Sales Drawings - 10090832](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-VG5-SPEC-EN | REV 6/2024