



Ergonomic Full Cycle Ratchet
Hand Crimper Kit: Y122CMR,
carrying case, select YA-L, YAV,
YAV-L, YS-L, and YSV Standard
Barrel terminals and splices

By Burndy
Catalog # [Y122CMRCIKIT](#)



Ergonomic Full Cycle Ratchet Hand Crimper Kit: Y122CMR,
carrying case, select YA-L, YAV, YAV-L, YS-L, and YSV
Standard Barrel terminals and splices.

Application

Crimping

General

Application - For Use On	#12-2 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Catalog Number	Y122CMRCIKIT
Die Type	Rotating Die Wheel
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	621945449541
UPC 12 Digit	6219454495411

Dimensions

Dimension - Thread Size	-
Dimensions	17.85 in x 7.38 in x 2.06 in
Height	2.06 in
Length	17.85 in
Weight	13 lb
Width	7.38 in

Conductor Related

Crimping Ranges	#12 AWG - #2 AWG Copper Stranded, Solid, and Flex
-----------------	---

Logistics

Package Contents	(1 each) Y122CMR, Y1MRKITCASE, Y122CMRSOMI, (15 each) YAV10T3, YA8CL, YA8CL1, YA6CL, YAV6CLTC14FX, YA4CL, YAV4CLTC516FX, YA2CL, YAV2CLTC516FX, YSV10, YS8CL, YS6CL, YS4CL, YS2CL
------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50061862](#)



A proud member of the Hubbell Family.