



4.5-Ton Remote C-Head, Pump/Hose, 6,000 psi, Uses D Dies, MIL-T-7928, UL/CSA

By Burndy
Catalog # [Y29BH](#)

4.5T Remote C-Head, Pump/Hose, 6,000 psi, MIL-T-7928,
UL/CSA.



Application

Crimping

General

Application - For Use On	Copper Insulated and Uninsulated, MIL-T-7928
Catalog Number	Y29BH
Crimp Force Capacity	4.5 ton
Die Type	D Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810039038
UPC 12 Digit	7818100390388

Dimensions

Dimensions	10.75 in x 1.25 in x 3.00 in
Height	3 in
Jaw Width	1.15 in
Length	10.75 in
Weight	5 lb
Width	1.25 in

Conductor Related

Crimping Ranges	Copper #8 - 2/0 AWG Code/Flex, Copper #8 - 4/0 AWG
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool, Metal Case
------------------	------------------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_Y29BH_Lineart](#)
[Sales Drawings - SC205962](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-Y29BH-SPEC-EN | REV 6/2024