



# 9-Ton Remote C-Head Crimper, For Navy and Commercial Cable, Rubber Covered

By Burndy  
Catalog # Y34BH



9-Ton Remote C-Head Crimper, Operating Pressure 10,000 psi, Uses B Dies, For Navy and Commercial Cable #4 AWG-500 kcmil, Rubber Covered.

## Application

Crimping

## General

Application - For Use On	Copper, Welding, N40-N500 Navy, Flexible and Extra Flexible, Aircraft Cable
Catalog Number	Y34BH
Crimp Force Capacity	9 ton
Die Type	B Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810408544
UPC 12 Digit	7818104085444

## Dimensions

Dimensions	16.75 in x 3.00 in x 3.00 in
Height	3 in
Jaw Width	1.10 in
Length	16.75 in
Weight	8 lb
Width	3 in

## Conductor Related

Crimping Ranges

Copper #4 - 500 kcmil code cable, Welding Cable: 350 kcmil, N40 to N500 Navy Cable, Flexible and Extra Flexible #4 - 4/0 Aircraft Cable; HYCRAB™ BURNDY® Network Connector System- Copper: #4 - 500 kcmil str., Aluminum: #6 - 300 kcmil

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool, Metal Case

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OVPF\\_Y34BH\\_lineart](#)  
[Sales Drawings - 201515](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-Y34BH-SPEC-EN | REV 6/2024