



# 11-Ton Dieless Remote C-Head Crimper with Male Couplers

By Burndy  
Catalog # [Y444SBH](#)



11-Ton Dieless Remote C-Head Crimper, with male couplers and canvas carry bag, Operating Pressure 10,000 psi.

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Catalog Number	Y444SBH
Crimp Force Capacity	11 ton
Die Type	Dieless
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	621945488021

## Dimensions

Dimensions	3.2 in x 13.7 in x 16.9 in
Height	16.9 in
Length	3.2 in
Width	13.7 in

## Logistics

Package Contents	Tool, Nylon Carry Bag
------------------	-----------------------

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50060031](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-Y444SBH-SPEC-EN | REV 6/2024