



15-Ton Remote C-Head Crimper, 10000 psi, Female Coupler.

By Burndy
Catalog # [Y46LWSBHF](#)



15-Ton Remote C-Head Crimper, Operating Pressure 10000 psi,
Uses P and U Dies with PUADP1 Adapter, Female Coupler.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46LWSBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673720
UPC 12 Digit	7818106737200

Dimensions

Height	14.68 in
Length	14.68 in
Weight	14.5 lb

Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	UI
---------------------------------------	----

Logistics

Package Contents	Tool, Nylon Carry Bag
------------------	-----------------------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50024880](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-Y46LWSBHF-SPEC-EN | REV 6/2024