



# 12-Ton Remote C-Head Crimper, Operating Pressure 10000 psi, Uses U Dies

By Burndy  
Catalog # [Y750BHXT](#)

12-Ton Remote C-Head Crimper, Operating Pressure 10000 psi,  
Uses U Dies.



## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Catalog Number	Y750BHXT
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810458594
UPC 12 Digit	7818104585944

## Dimensions

Dimensions	12.8 in x 5.2 in x 2.9 in
Height	2.9 in
Jaw Width	1.65 in
Length	12.8 in
Weight	10.8 lb
Width	5.2 in

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool, Nylon Carry Bag

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_Y750BHXT\\_lineart](#)  
[Sales Drawings - 10088816](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-Y750BHXT-SPEC-EN | REV 6/2024