



# YA29, 250 kcmil, CU, 1-hole, 1/2" Stud, Long Barrel

By Burndy  
Catalog # YA29

250 kcmil CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, 16 Die Index.



## Application

Wire Termination

## General

Catalog Number	YA29
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	16
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810504055
UPC 12 Digit	7818105040555

## Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.26 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.1 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	0.5 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[3D Models - YA29\\_MODEL-IGES](#)  
[3D Models - YA29\\_MODEL-PDF](#)  
[3D Models - YA29\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - sd079849-05](#)  
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/2  
Dimension - Z (inch) 0.55 in  
Physical Attribute - Tongue Angle Straight

---



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YA29-SPEC-EN | REV 6/2024