



## Compression Terminal

By Burndy  
Catalog # YA30L2TC38FX

250 kcmil, G,H CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.



### Application

Wire Termination

### General

Catalog Number	YA30L2TC38FX
Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810041819
UPC 12 Digit	7818100418199

### Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.43 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Flex G Size	250 KCMIL
Conductor - Copper Flex G Size Range	250 kcmil
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex H Size Range	250 kcmil
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - SE..208119-01](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YA30L2TC38FX-SPEC-EN | REV 6/2024