

Compression Terminal

By Burndy
Catalog # YA31L2TC38

350 kcmil CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Red Color Code, 18 or 324 Die Index.



Application

Wire Termination

General

| | |
|--------------------------------------|-----------------------------|
| Catalog Number | YA31L2TC38 |
| Color Code | Red |
| Connector Type | STANDARD BARREL |
| Die Index | 18 |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYDENT |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810503683 |
| UPC 12 Digit | 7818105036833 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-1/16 in |
| Dimension - B Length inch | 1.06 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - L Length Overall mm | 89 mm |
| Dimension - Length Overall inch | 3.51 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.88 in |
| Dimension - Pad Width inch | 1.29 in |
| Dimension - Strip Length inch | 1-1/8 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Stud Size inch | 0.375 in |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-----------------------------------|---------------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Navy Size | 350 (91) Navy |
| Conductor - Copper Str Size | 350 KCMIL |
| Conductor - Copper Str Size Range | 350 kcmil |
| Conductor - Material | COPPER |
| Conductor Size | 350 KCMIL |
| Conductor Type | CODE |

Certifications And Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [3D Models - YA31L2TC38_MODEL-STEP](#)
- [3D Models - YA31L2TC38_MODEL-PDF](#)
- [3D Models - YA31L2TC38_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD035209-10](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 3/8
Dimension - Z (inch) 0.42 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YA31L2TC38-SPEC-EN | REV 6/2024