



YA44A3, Al Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, AL9CU, 1000 kcmil

By Burndy
Catalog # [YA44A3](#)



AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

Application

Wire Termination

General

Catalog Number	YA44A3
Color Code	Brown
Connector Type	DUAL RATED
Die Index	302
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	ALUMINUM
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A
UPC	781810763001
UPC 12 Digit	7818107630011

Dimensions

Dimension - B Length fraction	2-3/4 in
Dimension - B Length inch	2.74 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.15 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.76 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	1.65 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	1000 KCMIL
Conductor - AL Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	1000 KCMIL
Conductor Type	CODE
Wire Size	1000 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Pallet Quantity	1960

Product Assets

[3D Models - YA44A3_MODEL-IGES](#)
[3D Models - YA44A3_MODEL-PDF](#)
[3D Models - YA44A3_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Aluminum Installation Instructions](#)
[Sales Drawings - SD073935-01](#)

Dimension - Strip Length inch 3
Dimension - Stud Size fraction 1/2
Dimension - Stud Size inch 1/2
Dimension - Thread Size 1/2
Dimension - Z (inch) 0.77 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YA44A3-SPEC-EN | REV 6/2024