



YA44L2TC38FX, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel, 750 kcmil G, H, 777 DLO

By Burndy
Catalog # [YA44L2TC38FX](#)



750 kcmil G,H,777 DLO CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, L115 Die Index.

Application

Wire Termination

General

Catalog Number	YA44L2TC38FX
Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	L115
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810020999
UPC 12 Digit	7818100209999

Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.74 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.19 in
Dimension - Strain Length inch	1-5/8 in

Conductor Related

Conductor - Copper DLO Size	777 KCMIL
Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper Flex G Size Range	750 kcmil
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex H Size Range	750 kcmil
Conductor - Copper Flex I Size	750 KCMIL
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	1960

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

Dimension - Strip Length inch 1-5/8 in
Dimension - Stud Size fraction 3/8
Dimension - Stud Size inch 3/8 in
Dimension - Thread Size 3/8
Dimension - Z (inch) 0.53 in
Physical Attribute - Tongue Angle Straight

[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE..208119-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YA44L2TC38FX-SPEC-EN | REV 6/2024