

Compression Terminal

By Burndy
Catalog # [YA4CA1](#)



AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

Application

Wire Termination

General

Catalog Number	YA4CA1
Color Code	Green
Connector Type	DUAL RATED
Die Index	375
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	ALUMINUM
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A, Dual Rated
UPC	781810751855
UPC 12 Digit	7818107518555

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.75 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.13 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.43 in
Dimension - Pad Width inch	0.47 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	4 AWG
Conductor Type	CODE
Wire Size	4 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [3D Models - YA4CA1_MODEL-IGES](#)
- [3D Models - YA4CA1_MODEL-PDF](#)
- [3D Models - YA4CA1_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Installation Manuals - Aluminum Installation Instructions](#)
- [Sales Drawings - SD073935-01](#)

Dimension - Strip Length inch 7/8
Dimension - Stud Size fraction 1/4
Dimension - Stud Size inch 1/4
Dimension - Thread Size 1/4 in
Dimension - Z (inch) 0.42 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YA4CA1-SPEC-EN | REV 6/2024