



Nylon Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # [YAE10NM](#)

Terminal - Nylon Insulated, Ring Tongue Multi-Finger Insulation Grip, 12 AWG - 10 AWG, #8-#10 stud, Tin Plated, Reel Packaging



Application

Power Connector

General

Catalog Number	YAE10NM
Color Code	Yellow
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring Terminal
Plated	Y
Plating Type	Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810028650
UPC 12 Digit	7818100286500

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	#8-#10
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Standards - Industry Standards Met	- UL486 - Military Specified (Mil-Spec)

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Packaging Type	Reel
----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAE10NM_LineArt](#)
[Sales Drawings - 50105268](#)



A proud member of the Hubbell Family.

