



# Compression Terminal

By Burndy  
Catalog # [YAEBAF27NTNOEM](#)

Cu T-Type Battery Post Connector Terminal, 3/0 AWG, Orange, 14 Index, 1-9/32 IN Strip Length, Polarity N.



## Application

Battery Post Terminal

## General

Catalog Number	YAEBAF27NTNOEM
Color Code	Orange
Connector Type	BATTERY T-POST
Die Index	14
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810562956
UPC 12 Digit	7818105629566

## Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Str Compact Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Sales Drawings - 50004536](#)  
[SDS - Anti-Seize Lubricants SDS](#)



A proud member of the Hubbell Family.