



# Compression Terminal

By Burndy  
Catalog # [YAEBAF28NTN](#)

Cu T Type Battery Post Connector Terminal, 4/0 AWG, 2.36" L, 1.97" W, Yellow.



## Application

Battery Post Terminal

## General

Catalog Number	YAEBAF28NTN
Color Code	Purple
Connector Type	BATTERY T-POST
Die Index	15
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810562499
UPC 12 Digit	7818105624999

## Dimensions

Dimension - Diameter Min Size	0.60 in
inch	
Dimension - L Length Overall	60 mm
mm	
Dimension - Length Overall	2.36 in
inch	
Dimension - Strip Length inch	1-9/32
Physical Attribute - Tongue	Straight
Angle	

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Compact Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Sales Drawings - 50004536](#)  
[SDS - Anti-Seize Lubricants SDS](#)



A proud member of the Hubbell Family.

