



Compression Terminal

By Burndy
Catalog # [YAEBAS2CNTNOEM](#)

Cu Battery Post Connector Terminal, #2 AWG, Brown, 10 Index, 1-3/32 IN Strip Length, Polarity N.



Application

Battery Post Terminal

General

Catalog Number	YAEBAS2CNTNOEM
Color Code	Brown
Connector Type	BATTERY STRAIGHT POST
Die Index	10
Finish Type	Tin-Plated
Installation Torque Recommended in-lb	72 LBS/in
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810547410
UPC 12 Digit	7818105474100

Dimensions

Dimension - Inside Diameter inch	0.340 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.30 in
Dimension - Outside Diameter inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Compact Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Sales Drawings - 50004535](#)
- [SDS - Anti-Seize Lubricants SDS](#)



