

Compression Terminal

By Burndy
Catalog # [YAEBAS6CNTN](#)

Battery Post HYDENT Cu Terminals, #6 AWG, 2.30" L, 0.98" W, Blue, Wire Strip Length - 1-3/32" L.



Application

Battery Post Terminal

General

Catalog Number	YAEBAS6CNTN
Color Code	Blue
Connector Type	BATTERY STRAIGHT POST
Die Index	7
Finish Type	Tin-Plated
Installation Torque Recommended in-lb	72 LBS/in
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810562512
UPC 12 Digit	7818105625122

Dimensions

Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.30 in
Dimension - Strip Length inch	1-3/32 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Str Compact Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Sales Drawings - 50004535](#)
[SDS - Anti-Seize Lubricants SDS](#)

