



Nylon Fork Terminal For 12 - 10 AWG

By Burndy
Catalog Number [YAES10N56F](#)



Nylon Insulated CU Fork Tongue Terminal, Wire Range: 12-10 AWG, Stud Size: #6 - #8, Package: Bulk, Strip Length: 11/32 IN.

General

Application	Power Connector
Color Code	Yellow
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES-F
UPC	781810805084
UPC 12 Digit	7818108050844

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Inside Diameter inch	0.22 in
Dimension - Length Overall inch	1.01 in
Dimension - N inch	0.17 in
Dimension - Outside Diameter inch	0.32 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094172](#)
[Technical Solutions - BURNDY_YAES10N56F_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAES10N56F-SPEC-EN | REV 11/2023

