



YAES14K10, Radiation Resistant Insulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAES14K10](#)



Radiation Resistant Insulated Ring Terminal For 16 - 14 AWG.

Application

For Class 1E Critical Circuits And Non-Critical Nuclear Associated Applications

General

Catalog Number	YAES14K10
Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Kynar
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Radiation Resistant KYNAR Ring Tongue
UPC	781810027059
UPC 14 Digit GTIN	00781810027059

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.45 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	IEEE 323
Standards - Industry Standards Met	IEEE 323
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAES14K7_LineArt](#)
[Sales Drawings - 50094159](#)
[Specifications - YAES14K10 Specification Sheet French](#)
[Specifications - YAES14K10 Specification Sheet English](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_CA-YAES14K10-SPEC-EN | REV 4/2025