



Compression Terminal

By Burndy

Catalog # [YAGB25LTC38FXOEM](#)

Cu Tubing Hylug, 1/0 AWG, 3/8 IN Stud.



Application

Wire Termination

General

Catalog Number	YAGB25LTC38FXOEM
Color Code	Pink
Connector Type	GROUNDING/STARTER LUGS
Construction Material - Main	Copper
Die Index	12
EU RoHS Indicator	Contact Manufacturer
Finish Type	Electro Tin plated
Material	COPPER
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810547434
UPC 12 Digit	7818105474344

Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.93 in
Dimension - Pad Width inch	0.93 in
Dimension - Stud Size fraction	3/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Sales Drawings - 30008293](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAGB25LTC38FXOEM-SPEC-EN | REV 6/2024