

Compression Terminal

By Burndy
Catalog # YAL1CT12

Copper HYLUGTM , Single Hole w/ Inspection Window, #1 AWG, 1/2" Stud,11 index,Green, Short Barrel,Electro- Tin Plated.



Application

Wire Termination

General

Color Code	Green
Connector Type	STANDARD BARREL
Die Index	11
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810416877

Dimensions

Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.14 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.37 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.73 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSD029213](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAL1CT12-SPEC-EN | REV 6/2024